

ALRO

Protective suit care in a systematic way



Cleaning,
Disinfection
and
Drying
Cabin

CDDC



The CDDC is used for the treatment of full protective suits as well as boots, gloves and respirator masks.

AXEL ROTHER
Montage und Dienstleistung
Heckenstr. 2
D-74706 Osterburken

Phone - Nr.: +49 6292 929202
Fax.-Nr.: +49 3222 4057030

E-Mail: alro-osterburken@t-online.de
Homepage: www.alroservice.eu

Protective suit care made easy



Cleaning, Disinfection and Drying Cabin for a maximum of 2 treatment spaces.
Display incl. user terminal and adjustable processing times.

Technical data for the Cleaning, Disinfection and Drying Cabin

CDDC 1-4

Measurements:	
Length	: 1800 - 3100 mm
Width	: 1520 mm
Height	: 2500 mm

Water supply	: ¾" outside thread
Wastewater channel	: ¾" outside thread
Wastewater tank	: ¾" outside thread
Electrical connection	: 230/400 V 32A
Pump power	: 0,7 kW
Heater, water	: 10 kW
Heater, air	: 6 kW

AXEL ROTHER
Montage und Dienstleistung
Heckenstr. 2
D-74706 Osterburken

Phone - Nr.: +49 6292 929202
Fax.-Nr.: +49 3222 4057030

Advantages of the CDDC-System:

- the modular construction of the cabin allows flexibility to existing buildings
- full automatic operation, controlled by series-parallel-series memory
- the operation is appropriate for the material involved
- highly efficient cleaning and disinfection
- requires less space
- not harmful to the environment because of recirculation operation and the use of ecologically beneficial agents
- user-friendly
- low-maintenance
- hot water system with temperature control unit
- illumination of the washroom when the door opens
- intensive and all surface reaching cleaning guaranteed with moving spraying system
- all processing times are adjustable by using the display incl. user terminal. This way, the operation can be adjusted to the different cleaning and disinfection procedures.
- aeration of the washroom during the disinfection process
- CE-conformity, DIN-standard
- emergency shutdown
- contact-free door switch
- high-performance output blower with thermal protection
- Heater battery with triple overheating protection
- drying temperature adjustable
- self-priming pump with filter system and flush unit
- dual wastewater disposal system (wastewater channel or external tank)
- automatic dosage system for disinfectants (For example for the use of drying agents). The amount can be individually adjusted.
- special bow build in aluminium with spraying and drying system to carry and handle the protective suits, with air and water connectors
- special head pumps (2 for each suit) to remove the water out of the head of the suit
- overflow safety switch

E-Mail: alro-osterburken@t-online.de
Homepage: www.alroservice.eu