

Quantity Description Pos.

1 DRTK-M1 disinfection, cleaning and drying cabinet for 12 breathing masks, 6 lung regulators

Fully automatic disinfection, cleaning and drying cabinet for the simultaneous care of up to 12 breathing masks, with additional equipment also 6 lung regulators These systems are very environmentally friendly thanks to the recirculation process used and the use of environmentally friendly cleaning agents and disinfectants. The helmets pass through a water curtain for cleaning and disinfection.

During drying, air is blown directly onto or into the helmets

with the following technical data:

Cabin:

- Aluminium profile housing for better sound insulation and thermal insulation for optimal energy utilisation Powder-coated on both sides, resulting in almost no maintenance required
- Stainless steel drip tray
- Cover grille over the heating elements in stainless steel design
- Water extraction from below, resulting in no residual water in the tray area
- Single-pane safety glass door
- Contactless door contact switch
- 4 adjustable feet

Width: approx. 800 mm Depth: approx. 800 mm approx. 1355 mm Height: Weight: approx. 120 kg

1/3

AXEL ROTHER Engineering Gartenweg 11 74743 Seckach

Telefon - Nr.: 06292/929 202 UST.ID.:

DE263476717

Homepage: www.al-ro.de E-Mail: info@al-ro.de Bankverbindung:

IBAN

BIC:

DE50660691030025026438

Raiffeisenbank EG Elztal

GENODE61ELZ



Washing:

- Rotating wheel with mounting adapter for 12 masks
- Powerful self-priming pump
- Tested standard washing programme A pre-wash with clean water, a disinfectant cleaning wash and 4 x rinses with clean water

Drying:

- High-performance fan with thermal protection
- 1.8 kW heating coil with triple protection against overheating

Disinfection:

- Automatic dosing device with low-maintenance peristaltic pump and suction lance
- 2.5 kW hot water preparation to ensure disinfection and cleaning performance.

Controls and displays:

- Siemens touch panel
- Siemens control system for quick commissioning with integrated basic settings and standard programmes
- The control panel features the following functions:
- Touch panel with visual menu navigation
- Emergency stop mushroom button
- On/off switch
- Complete cycle including drying approx. 60 90 min.

Homepage:

E-Mail:

Bankverbindung:



Safety features:

- Level control with integrated overflow protection
- Automatic shut-off in case of malfunction
- Low voltage 24V
- Safety thermostats for water and air

Connections:

Water connection: 3/4 external thread Waste water connection: 3/4 external thread Exhaust air connection: 125 mm diameter Electrical connection: 230V 50Hz

Our products are subject to continuous development. We reserve the right to change the design, execution and materials at short notice and without prior notice. As of 2025

3/3

AXEL ROTHER Engineering Gartenweg 11 74743 Seckach

Telefon - Nr.: 06292/929 202 UST.ID.: Homepage:

DE263476717 www.al-ro.de

Bankverbindung:

Raiffeisenbank EG Elztal

DE50660691030025026438

E-Mail: BIC: GENODE61ELZ info@al-ro.de

IBAN